

Datasheet

AHSA1 purified MaxPab rabbit polyclonal antibody (D01P)

Catalog Number: H00010598-D01P

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against a full-length human AHSA1 protein.

Immunogen: AHSA1 (NP_036243.1, 1 a.a. ~ 338 a.a) full-length human protein.

Sequence:

MAKWGEGDPRWIVEERADATNVNNWHWTERDASN
WSTDKLKLFLAVQVQNEEGKCEVTEVSKLDGEASIN
NRKGKLIFFYEWSVKLNWTGTSKSGVQYKGHVEIPNL
SDENSVDVEISVSLAKDEPDNLVALMKEEGVKLLRE
AMGIYISTLKTEFTQGMILPTMNGESVDPVGQPALKTE
ERKAKPAPSKTQARPVGVKIPTCKITLKETFLTSPPELY
RVFTTQELVQAFTHAPATLEADRGGKFHMVDGNVSG
EFTDLVPEKHIVMKWRFKSWPEGHFATITLTFIDKNGE
TELCMEGRGIPAPEEERTRQGWQRYFFEGIKQTFGY
GARLF

Host: Rabbit

Reactivity: Human

Applications: WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 10598

Gene Symbol: AHSA1

Gene Alias: AHA1, C14orf3, p38