

Datasheet

FZD10 polyclonal antibody

Catalog Number: PAB20734

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant FZD10.

Immunogen: Recombinant protein corresponding to amino acids of human FZD10.

Sequence:

KTLQSWQQVCSRRLKKKSRRKPASVITSGGIYKKAQH
PQKTHHGKYEIPAQSPTCV

Host: Rabbit

Reactivity: Human

Applications: IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry (1:10-1:20)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.
Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 11211

Gene Symbol: FZD10

Gene Alias: CD350, FZ-10, FzE7, hFz10

Gene Summary: This gene is a member of the frizzled gene family. Members of this family encode 7-transmembrane domain proteins that are receptors for the Wingless type MMTV integration site family of signaling proteins. Most frizzled receptors are coupled to the beta-catenin canonical signaling pathway. Using array analysis, expression of this intronless gene is significantly up-regulated in two cases of primary colon cancer. [provided by RefSeq]