




## TMEM5 Antibody

CATALOG NUMBER: 48-201



Immunohistochemistry staining of TMEM5  
in ovary, oocytes tissue using TMEM5  
Antibody.

### Specifications

<b>SPECIES REACTIVITY:</b>	Gibbon, Gorilla, Human
<b>TESTED APPLICATIONS:</b>	IHC
<b>APPLICATIONS:</b>	TMEM5 antibody can be used in ELISA, Western Blot, and immunohistochemistry starting at 5 ug/mL.
<b>USER NOTE:</b>	Optimal dilutions for each application to be determined by the researcher.
<b>SPECIFICITY:</b>	BLAST analysis of the peptide immunogen showed no homology with other human proteins, except CACYBP (50%).
<b>IMMUNOGEN:</b>	TMEM5 antibody was raised against a peptide located near the Extracellular domain of TMEM5 (Human).
<b>HOST SPECIES:</b>	Rabbit

### Properties

<b>PURIFICATION:</b>	Immunoaffinity Chromatography
<b>PHYSICAL STATE:</b>	Liquid
<b>BUFFER:</b>	PBS, 0.1% sodium azide.
<b>STORAGE CONDITIONS:</b>	TMEM5 antibody should be stored long term (months) at -80 °C and short term (days) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
<b>CLONALITY:</b>	Polyclonal
<b>CONJUGATE:</b>	Unconjugated

### Additional Info

<b>ALTERNATE NAMES:</b>	TMEM5, HP10481, Transmembrane protein 5
<b>ACCESSION NO.:</b>	Q9Y2B1
<b>PROTEIN GI NO.:</b>	50401708
<b>OFFICIAL SYMBOL:</b>	TMEM5
<b>GENE ID:</b>	10329

### Background

