

Datasheet

RNF130 polyclonal antibody

Catalog Number: PAB20735

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant RNF130.

Immunogen: Recombinant protein corresponding to amino acids of human RNF130.

Sequence:

PWLSEHCTCPMCKLNILKALGIVPNLPCTDNVAFDMER
LTRTQAVNRRSA

Host: Rabbit

Reactivity: Human

Applications: IF, IHC-P, WB

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:200-1:500)

Western Blot (1:250-1:500)

Immunofluorescence (1-4 ug/mL)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 55819

Gene Symbol: RNF130

Gene Alias: G1RZFP, GOLIATH, GP, MGC117241, MGC138647, MGC99542

Gene Summary: The protein encoded by this gene contains a RING finger motif and is similar to g1, a Drosophila zinc-finger protein that is expressed in mesoderm and involved in embryonic development. The expression of the mouse counterpart was found to be upregulated in myeloblastic cells following IL3 deprivation, suggesting that this gene may regulate growth factor withdrawal-induced apoptosis of myeloid precursor cells. [provided by RefSeq]